

ss

Technical drawing showing the front view of a cabinet. The overall width is 99.5 [3.917"] and the overall height is 450 [17.716"]. The distance between the internal faces of the front and rear panels is 406 [15.984"]. The width of the front panel is 190 [7.480"] and the width of the rear panel is 170.88 [6.727"] (including the foot kit assembly). The drawing includes a central vertical line and a circular detail with four screws.

450 [17.716"]

406 [15.984"] = distance between internal faces
of front & rear panels

170.88 [6.727"]
<inc foot kit assembly>

Technical drawing of a table showing dimensions and a grid. The overall width is 514.93 [22.050] and the overall height is 516.25 [20.325]. The drawing includes a grid of small circles and various adjustment points indicated by arrows and symbols.

516.25 [20.325"]

157.26 [6.191"]

Tolerances unless otherwise stated:	Required Finish:	Scale: 1:1	ALL DIMENSIONS IN MILLIMETRES		DO NOT SCALE
	See notes	Drawn by: Ian Cox	Checked By:	Drawing Number --	Date drawn: Nov '07
General tolerances ±0.20			METCASE ENCLOSURES		
Resultant tolerances between hole centers ±0.15			15 Brunel Way Segensworth East, Fareham, Hampshire, PO15 5TX, UK.		
Tolerances on hole diameters ±0.05	www.metcase.com		Part Name Instrumet 3U x 19" x 450mm - Carry Handle		
Angles ± 0.5°			Part Number M6019335		Sheet 1 of 1
Surface finish 32/	©OKW ENCLOSURES LTD (DATE AS SHOWN). THIS DRAWING CONTAINS PROPRIETARY INFORMATION OF OKW ENCLOSURES LTD AND IS TENDERED SUBJECT TO THE FOLLOWING CONDITIONS: THE INFORMATION BE RETAINED IN CONFIDENCE, NOT BE REPRODUCED OR COPIED, AND NOT BE USED OR INCORPORATED IN ANY PRODUCT, UNLESS PERMISSION IS OBTAINED IN WRITING FROM OKW ENCLOSURES LTD.				
	A2				