

Product Datasheet

Aluminium Cable Clip



Product Specifications

Maximum Cable Diameter	: 10 mm
Clip Material	: Aluminium
Base Material	: Polyethylene : : Pad-self adhesive
Adhesive Base	: Acrylic
Holding Power (hr/kg × 25mm ²)	: 80° / 0.5 kg / 24 hrs : : 25° / 1 kg × 24 hrs
Temperature Range	: -10°C to 90°C
180° Peel Adhesion (kg/25 mm)	: 25 kg

RS Number	Length (mm)	Width (mm)	Height (mm)	Max Bundle Dia. (mm)
475-198	16	10.6	9.4	6
475-160	19	16	14.9	9.5