



DV20VB Impact Drill

Two speed/Variable speed/
Reverse/Two mode/Keyless chuck

Capacity:

Masonry	Low 20mm	High 13mm
Steel	Low 13mm	High 8mm
Wood	Low 40mm	High 25mm

Chuck Capacity 13mm

Power Input 750W (230V), 730W (110V)

No-Load Speed 0-1100, 0-2600/min

Full-Load Impact Rate 0-14000, 0-36000/min

Overall Length 350mm

Weight 2.65kg

Standard Accessories: side handle, depth stop, carrying case.