

## Fluorescent High Durability Lighthouse-R.S. 266-2767.

Features:-Excellent light quality; High strength;Weather proof;\_High\_efficiency;Low running cost;Minimum maintenance;Low running temperature.

### Mechanical.

Construction:-High pressure die-cast aluminium case.Finish:-black powder coat.

Polycarbonate lens.

Dimensions:-Ht. 207mm;Width 265mm; Depth 100mm.

Weight:- 2.15kg.

Environmental protection:-I.P. 66.

Operating temp:- -20C.to +60C.

Connection:- 0.6 metre 3 core cable.

Mounting:-Universal 'stirrup' bracket allowing 130mm stand-off(if wall mounted).

Provision for standard 20mm conduit mounting.

Adjustment:-Friction wheels allow wide range of vertical adjustment.

### Electrical.

Light output:-1800 lumens.Wide angle c.160deg

Colour temp. 4000K.

Lamp type:-Compact fluorescent 11 watt,2 pin,G23.(R.S. 407-5604).

Operating voltage:-220/240v.a.c. 50/60Hz.

Input:- max.30 watts.

Circuit:- 2xmetal ballast.

N.B. This product must be earthed.

P.B. 1/07/03.