







MATERIAL NUMBER	WIRE AWG	INSUL DIA O.D.
845080001	18-14	.053(1.35) - .120(3.05)

ⓑ



LARGE POLARIZING KEY INDICATOR



SECTION Z-Z

NOTES:

1. MATERIALS: HOUSINGS: POLYESTER (PBT), GLASS FILLED, UL94V-0 & POLYETHERIMIDE (PEI), UNFILLED, UL94V-0. COLOR, UNLESS OTHERWISE SPECIFIED: BLACK
SEALS: SILICONE RUBBER
COLOR: RUST RED

2. PRODUCT SPECIFICATION: PS-84501-001.
3. MATES WITH: SERIES 84501 PLUG CONNECTOR.
4. USE CONNECTOR WITH FEMALE CRIMP TERMINAL SERIES 84590.
5. ALL COMPONENTS ARE ROHS COMPLIANT.
6. HEX NUT SOLD SEPARATELY, OPTIONAL FOR PANEL MOUNTING. MOLEX MATERIAL NUMBER 845020004.
7. RECOMMENDED PANEL THICKNESS .062/1.58 TO .187/4.76

UPDATE NOTES & TABLE EC NO: WNA2008-0139 DRAWN:WLEUNG 2008/02/27 CHKD:RDEROSS 2008/04/21 APPR:RDEROSS 2008/04/24		DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 1:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION 			
					mm	INCH	DRAWN BY DMYRICK	DATE 2006/6/26	RECPT. CONNECTOR ASSEMBLY, 18-14 POS SOCKET TERMINALS				
				4 PLACES	± ---	± ---	CHECKED BY JPAWLICKI	DATE 2006/6/26					
				3 PLACES	± ---	± .015	APPROVED BY RDEROSS		DATE 2006/6/26	MOLEX INCORPORATED			
				2 PLACES	± 0.38	± ---							
1 PLACE	± ---	± ---	ANGULAR ± ---°		MATERIAL NO.	DOCUMENT NO.	SHEET NO.						
B		REV		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-84508-001		1 OF 1			
						SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					