

## METAL SHEARS

The Bahco metal shear range helps you use the right shear to get your job done more efficiently. Whether working in heavy industry or doing lighter

metal-cutting jobs, you will find shears that are fit for purpose. The tables below will help you find the right tool for the job.

Recommendations may vary slightly for harder and extreme gauges.

Shears	Industrial branch							
	HV/ AC installation	Dry-wall installation	Ceiling installation	Roofing	Tech. insulation	Heavy industry	Warehouse strap-cutting	Discerning private usage
MA225	●●●	●●●						
MA225R	●●	●●	●●	●●	●●		●	
MA225L	●●	●●	●●	●●	●●		●	
MA321	●●	●●	●●	●●	●●		●	
MA311	●●	●●	●●	●●	●●		●	
MA325	●			●	●		●●●	
MA361	●			●	●		●●●	
MA351	●			●	●		●●●	
MA431		●	●					●●
MA421		●	●				●	●●
MA401		●	●				●	●●
MA411		●	●				●	●●
MR126		●●	●●				●●	●
MR227R	●●			●●	●●		●	●
MR227L	●●			●●	●●		●	●
MR340	●●			●●●	●●			●●
MR726		●	●					●
M126		●●	●●				●●	
M227R	●●			●●	●●		●	
M227L	●●			●●	●●		●	
M330	●●			●●				
M526		●	●	●				
M722		●	●	●				
M726		●	●	●				
M730		●	●	●				
8691				●	●			
583D	●●●			●●●	●●●			●●●
584D	●●●			●●●	●●●			●●●
585D	●●●			●●●	●●●			●●●
586D	●●●			●●●	●●●			●●●
M926	●●			●●	●●			
M676						●●●		
M6376						●●●		

highly recommended: ●●● / recommended: ●● / useful: ●



## MA421

## AVIATION/COMPOUND SHEARS



- Metal shears designed for occasional use by craftsmen and home use
- Cut sheet metal up to 1.5 mm
- Forged from steel containing chromium and molybdenum for good resistance
- Milled cutting edges, serrated and induction hardened to 60-62 HRC
- Lever system increases efficiency
- Handles with soft grip part and return spring to enhance the working comfort
- Yellow handles = straight cut
- Cutting capacity: 1 - Stainless steel, 2 - Cold rolled steel

MA421	0167616	4	250	0.7	1.2	405

Type of cut

Shears	Corner-snipping	Notching	Sharving	Left-cut	Right-cut	Straight through cut	Left hole-cut	Right hole-cut
MA225	ooo	ooo	ooo					
MA225R	oo	oo	oo		oo			o
MA225L	oo	oo	oo	oo			o	
MA321	oo	oo	oo		oo			o
MA311	oo	oo	oo	oo			o	
MA325	oo	oo	oo			oo		
MA361	oo	oo	oo		oo			
MA351	oo	oo	oo	oo				
MA431	oo	oo	oo			o		
MA421	oo	oo	oo			oo		
MA401	oo	oo	oo	o				
MA411	oo	oo	oo		o			
MR126	ooo	ooo	ooo					
MR227R	oo	oo	oo		oo			o
MR227L	oo	oo	oo	oo			o	
MR340	oo	oo	oo			ooo		
MR726	ooo	ooo	ooo					
M126	ooo	ooo	ooo					
M227R	oo	oo	oo		oo			o
M227L	oo	oo	oo	oo			o	
M330	oo	oo	oo			ooo		
M626	ooo	ooo	ooo					
M722	ooo	ooo	ooo					
M726	ooo	ooo	ooo					
M730	ooo	ooo	ooo					
8691	oo	oo	o		oo			
583D	ooo	oo	ooo	ooo		ooo	ooo	
584D	ooo	oo	ooo		ooo	ooo	ooo	ooo
585D	ooo	oo	ooo	ooo		ooo	ooo	
586D	ooo	oo	ooo		ooo	ooo		ooo
M626				o	o	oo		
M676	ooo	oo	o					
M6376	ooo	oo	o			ooo		

highly recommended: ooo / recommended: oo / useful: o