

## Cable binder base - WT-BASE P HF 9,5 BK - 3240710

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Cable binder base, for cable binders of up to 9.5 mm, with fins, 8 mm drilling diameter, can be knocked in

### Why buy this product



### Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 046356 704274
Weight per Piece (excluding packing)	2.01 g
Custom tariff number	39269097
Country of origin	Italy

### Technical data

#### Dimensions

Length (b)	20 mm
Height	43 mm
Width (a)	13 mm
Hole diameter	8.00 mm

#### Ambient conditions

Ambient temperature (operation)	-10 °C ... 65 °C
Ambient temperature (assembly)	-5 °C ... 65 °C

#### General

Color	black
Type	Fixing
Components	free from silicone and halogen
Inflammability class according to UL 94	HB

## Cable binder base - WT-BASE P HF 9,5 BK - 3240710

### Technical data

#### General

Material	PA 6
----------	------

### Classifications

#### eCl@ss

eCl@ss 4.0	27140702
eCl@ss 4.1	27140702
eCl@ss 5.0	27140702
eCl@ss 5.1	27140702
eCl@ss 6.0	27140702
eCl@ss 7.0	27140702
eCl@ss 8.0	27140702

#### ETIM

ETIM 3.0	EC000046
ETIM 4.0	EC000046
ETIM 5.0	EC000046

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703