


Deep groove ball bearings, single row, SKF Energy Efficient (E2) bearings



Principal dimensions			Basic load ratings		Fatigue load limit P_u	Speed ratings		Mass	Designation
d	D	B	dynamic	static		Reference speed	Limiting speed		
mm			kN		kN	r/min		kg	-
35	72	17	25,5	15,3	0,64	22000	12000	0,29	E2.6207-2Z/C3



Calculation factors

k_r 0,025
 f_0 14