

Cable gland - HC-DS-PG21-Z - 1772641

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Pressure screws, with strain relief clamps, nickel-plated brass, clamping area 12 mm ... 20 mm, type Pg21



Key commercial data

Packing unit	10 pc
GTIN	
Weight per Piece (excluding packing)	60.59 g
Custom tariff number	74153300
Country of origin	Germany

Technical data

Dimensions

Wrench size, union nut	34 mm
Clamping range of the strain relief clip	12.00 mm ... 20.00 mm

General

Material, pressure screw	Nickel-plated brass
Thread type on connection side	Pg21

Classifications

eCl@ss

eCl@ss 4.0	27141209
eCl@ss 4.1	27141209
eCl@ss 5.0	27149109
eCl@ss 5.1	27149109
eCl@ss 6.0	27149109
eCl@ss 7.0	27149109
eCl@ss 8.0	27149109

Cable gland - HC-DS-PG21-Z - 1772641

Classifications

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000441

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	39121408

Approvals

Approvals

Approvals

GOST

Ex Approvals

Approvals submitted

Approval details

GOST

Drawings

Dimensioned drawing



