



XVGB3SH

Tower Light - RAG - 24V - LED - W.Buzzer - Tube mounting with fixing plate



Main

Range of product	Harmony XVG
Product or component type	Complete pre-wired monolithic tower light
Beacon or indicator bank unit type	3 illuminated units
Material	PC (UL94 V-2) globe ABS (UL94HB) tube body Aluminium tube
Mounting diameter	60 mm
Component name	XVG
Device mounting	Tube mounting with fixing plate
Light source	LED steady green LED steady red LED steady amber
Light block color	Red/amber/green
Indicator bank base type	Base with integrated buzzer

Complementary

[Us] rated supply voltage	24 V AC/DC
Cable cross section	0.33 mm ²
[Uimp] rated impulse withstand voltage	0.5 kV
Current consumption	180 mA
Noise level	85 dB
Power consumption	4.1 W
Fundamental frequency	2.64 kHz
Product weight	0.37 kg

Environment

Product certifications	CE
Ambient air temperature for storage	-35...70 °C
Ambient air temperature for operation	-10...50 °C
IP degree of protection	IP42

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Compliant - since 1140 - Schneider Electric declaration of conformity

Contractual warranty