

KYBKM-65CHMTU Stainless Steel Mini Keyboard with Trackball



Faceplate Dimensions(W X H): 330x100 mm

Basic Instructions

Support OS: Windows XP/Vista/7/8 and above, Linux and Unix
comply with ISO/IEC 9995、GB/T14081 standard
Keyboard made of high quality stainless steel
With 65 customized keys and trackball
Dustproof, waterproof, shake-proof and vandal proof

Applications:

Check-in Kiosk, Info-Kiosk, Internet Kiosk, Medical Kiosk, Industrial Control Platform.

Interface: PS/2 or USB

Mechanism Performance

Keyboard lifespan: more than 2 million
Force on keys: 3-5N
Key travel: >2.5mm
Diameter of trackball: 25mm

Environment adaptation

Protection Level: IP65 static /IP54 dynamic
Operating Temperature :
1. Economical Grade: 0°C~+45°C RH:30~90%,
2. Industrial Grade: -40°C~+60°C RH: 30~90%
Storage temperature(Recommended): -25°C~+55°C RH:20~95%(No condensate)
Maximum humidity in operating environment:90%
Air Pressure: 60-106 Kpa

Approvals:

RoHS,CE,FCC
IP65,IK07