

Lighting controls

Selection and ordering data

Version	DT	Order No.	Price per PU	PU (UNIT, SET, M)	PS*/P. unit	PG
General information <ul style="list-style-type: none"> • For stand-alone devices and combinations • For screw and claw fixing • Degree of protection: IP20 • Size of cover plates: 55 mm x 55 mm 						
Note	Section	Page				
• All cover plates for dimmers shown here can be combined with frames of the DELTA line product range, see ...	Design / DELTA line	2/5				
• All cover plates for dimmers shown here can be combined with the frames and color elements of the DELTA vita product range, see ...	Design / DELTA vita	2/5				
• All cover plates for dimmers shown here can be combined with frames of the DELTA miro product range, see ...	Design / DELTA miro	3/6				
Note Download the operating and mounting instructions at: http://support.automation.siemens.com/WWW/view/en/17738210/133300						

Rotary dimmers

Cover plates with rotary button, for dimmers



5TC8 900

Versions

- Titanium white (similar to RAL 9010)
- Electrical white (RAL 1013)
- Aluminum metallic (similar to RAL 9006)
- Carbon metallic (similar to RAL 7016)

Symbol	Inserts	Section	Page				
				A	5TC8 900	1	1/10 units 024
				A	5TC8 901	1	1/10 units 024
				A	5TC8 902	1	1/10 units 024
				A	5TC8 903	1	1/10 units 024
	Incandescent lamp dimmers, 50 ... 400 W	Functions / Switching/Pushbutton Control/Dimming	10/11	A	5TC8 256	1	1 unit 024
	Incandescent lamp dimmers, 50 ... 600 W, for two-way switching	dto.	10/12	A	5TC8 257	1	1 unit 024
	Low-voltage dimmers, for magnetic transformers, 50 ... 600 W,	dto.	10/12	A	5TC8 283	1	1 unit 024
	25 ... 500 VA,						
	for two-way switching						
	Low-voltage dimmers, for electronic transformers, 20 ... 600 W,	dto.	10/13	A	5TC8 284	1	1 unit 024
	20 ... 525 VA,						
	for two-way switching						
	Low-voltage dimmers, for electronic transformers, 60 ... 800 W,	dto.	10/13	A	5TC8 258	1	1 unit 024
	60 ... 800 VA,						
	for two-way switching						
	Electronic potentiometers, switch	dto.	10/15	A	5TC8 424	1	1 unit 024
	Electronic potentiometers, pushbutton	dto.	10/16	A	5TC8 425	1	1 unit 024