


LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
BD	35				J	REDRAWN	6-27-91	-
					K	REV PER ECN BD5454	05/26/92	KB
					L	SUPSD -3 & REV PER EC 0020-1080-95	17 OCT 95	RB
					M	REV AND REACTIVATE -3 PER EC 0020-419-96	07 MAY 96	AWF



1. 208486-1 MATES WITH AMP RECEPTACLE 208487-1 OR -2.
208486-3 MATES WITH AMP RECEPTACLE 208487-1 ONLY.
2. THIS PLUG ACCEPTS FOURTEEN (14) MULTIMATE PIN
CONTACTS. MAXIMUM WIRE INSULATION DIAMETER = .105.
3. AMP PART NUMBER AND DATE CODE TO BE LOCATED
ON COUPLING RING.

YES	208486-3
NO	208486-1
TETRASEAL	PART NUMBER

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± - MATERIAL SEE CALLOUT	DR 6-27-91 R.LEE BG	 AMP Incorporated Harrisburg, PA 17105-3608			
	CHK 4-20-92 W.G.LENKER				
	APPD 4-20-92 K.BEAVER	NAME PLUG ASSEMBLY, REV SEX, SERIES 1, 22-14, CMC			
	APPD 4-20-92 C.ROHDE				
	PRODUCT SPEC 108-10040				
FINISH SEE CALLOUT	APPLICATION SPEC -	SIZE 	CAGE CODE 00779	DRAWING NO 208486	
	WEIGHT -	SCALE 2:1		SHEET 1 OF 1	