



ENGLISH

Datasheet

RS Pro Tungsten Carbide Tipped 38mm Hole Saw, 13mm Cut Depth

RS Stock No: **673-4728**



Product Details

RS Pro hole saw has a diameter of 38 mm. It has tungsten carbide tip to work in the toughest applications. This saw drills holes of up to 13 mm depth.

Features and Benefits

- Carbide tipped hole saws
- 13mm depth of cut
- Shank diameter of 10 mm



ENGLISH

Specifications:

Arbor Included	Yes
Cut Depth	13 mm
Diameter	38 mm
Material	Tungsten Carbide Tipped
Shank Diameter	10 mm
Type	Hole Saw



HSS Metric Drill Bits Set 19pcs, fully ground, black finish,DIN338

RS Stock Number	Manufacture Part No.	Size	Package
6734709	H1995	1-10x0.5mm	Round Plastic Drum

22 piece HSS Metric Tap and Drill Set

RS Stock Number	Manufacture Part No.	Package	Content
6734702	T9222	Metal box	14pcs HSS Taps:M3-M4-M5-M6-M8-M10-M12 7pcs Drills: 2.5-3.3-4.2-5.0-6.8-8.5-10.2mm 1pc No.1 1/2 tap Wrench

Arborless Carbide Holesaw

RS Stock Number	Manufacture Part No.	Size (mm)	Depth of Cut mm	Shank Dia. mm
6734706	S10700160	16	13	10
6734715	S10700190	19	13	10
6734718	S10700200	20	13	10
6734712	S10700220	22	13	10
6734721	S10700250	25	13	10
6734724	S10700320	32	13	10
6734728	S10700380	38	13	10
6734737	S10700400	40	13	10
6734730	S10700510	51	13	10

HSS Conduit Holesaw

RS Stock Number	Manufacture Part No.	Size (mm)	Depth of Cut mm	Shank Dia. mm
6734743	S10600200	20	8	10
6734746	S10600250	25	8	10

Pilot Drills

RS Stock Number	Manufacture Part No.	Dia. (mm)	Overall Length mm	Application
6734734	S10700650	6.0	50	for Carbide Holesaw
6734740	S10600563	3/16"	65	for HSS holesaw