

Datasheet

Stock No: 491-910

RS Pro 3 Core Orange 3183Y Mains Power Cable



Permanoid spec. number 3183Y 4.0mm²

Description 56/0.3mm PCW 3 core PVC insulated and sheathed.

Conductors (4.0mm²) 56/0.3mm plain annealed copper.

Insulation PVC, 0.8mm nominal thickness, to 4.12mm nominal diameter.

Core colours 1) Blue 2) Brown 3) Green/Yellow.

Construction Cores 1 to 3 laid-up.

Sheath PVC, 1.2mm nominal thickness, to 11.3mm nominal diameter.

Sheath marking To be marked:-
'PERMANOID BASEC <HAR> H05VV-F'.

Rated Voltage 300/500

Current rating 25 amps.

Temp. Rating -15 to +70°C.

Harmonized code H05VV-F

Specification BS 7919 2001 Table 40.

BASEC Approved