




10 9 8 7 6 5 4 3 2 1



ITEM	COMPONENT	MATERIAL	FINISH
1	REC SHELL	BRASS	NICKEL PLATED
2	INSERT	PUR	BLACK
3	CONTACT	BRASS / GOLD	CuZn Ni/ Au
4	WIRES	COPPER/PVC	NONE
5	O-RING	NBR	BLACK
6	O-RING	VITON	RED
7	POTTING MATERIAL	EPOXY	NONE

Wiring Diagram:
1 - BROWN / braun
2 - WHITE / weiß
3 - BLUE / blau
4 - BLACK / schwarz



VOLTAGE RATING: 250 VAC / VDC
AMPERAGE RATING: 4 A
PROTECTION CLASS: IP 67/68/69K
OPERATING TEMPERATURE: -25°C / 90°C
UL CERTIFICATION: FILE NO. E152210
CSA CERTIFICATIONS: FILE NO. LR6837

POL MATERIAL NO. ENGINEERING NO. FINISHED LENGTH
4 1200845107 WR4U20E03C3003 300 ±10

ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
EC NO: WEU2010-0298		DRAWN: STAUDIGEL		mm		MM ONLY		2:1	METRIC	THIRD ANGLE PROJECTION	
2010/01/29		2010/02/01		INCH		DRAWN BY		DATE		TITLE	
CHKD:		2010/02/01		4 PLACES ±---		NSTAUDIGEL		2010/01/29		RECEPTACLE FEMALE M12-4P	
APPR: FPACHER		2010/02/02		3 PLACES ±---		CHECKED BY		DATE		ULTRA-LOCK FRONT M16X1.5	
				2 PLACES ±0.05		APPROVED BY		DATE		MOLEX INCORPORATED	
				1 PLACE ±0.1		FPACHER		2010/02/01		DOCUMENT NO.	
				ANGULAR ±---°		MATERIAL NO.				SD-120084-024	
				DRAFT WHERE APPLICABLE		SIZE				SHEET NO.	
				MUST REMAIN		A3				1 OF 1	
				WITHIN DIMENSIONS							