

	Series 4 			Series 5 			Series 22 			Series 13 				
														
Copper tubular cable lugs and connectors Series L	HL46	6 mm ²		HL5635	6 + 35 mm ²		L226	6 mm ²			HL136	6 mm ²		
	HL410	10 mm ²		HL51050	10 + 50 mm ²		L2210	10 mm ²			HL1310	10 mm ²		
	HL416	16 mm ²		HL51670	16 + 70 mm ²		L2216	16 mm ²			HL1316	16 mm ²		
	HL425	25 mm ²		HL52595	25 + 95 mm ²		L2225	25 mm ²			HL1325	25 mm ²		
	HL435	35 mm ²		HL5120	120 mm ²		L2235	35 mm ²			HL1335	35 mm ²		
	HL450	50 mm ²		HL5150	150 mm ²		L2250	50 mm ²			HL1350	50 mm ²		
	HL470	70 mm ²		HL5185	185 mm ²		L2270	70 mm ²			HL1370	70 mm ²		
	HL495	95 mm ²		HL5240	240 mm ²		L2295	95 mm ²			HL1395	95 mm ²		
	HL4120	120 mm ²					L22120	120 mm ²			HL13120	120 mm ²		
	HL4150	150 mm ²					L22150	150 mm ²			HL13150	150 mm ²		
							L22185	185 mm ²			HL13185	185 mm ²		
							L22240	240 mm ²			HL13240	240 mm ²		
							L22300	300 mm ²			HL13300	300 mm ²		
											HL13400	400 mm ²		
Stainless steel and nickel tubular cable lugs and connectors	HN4051	0.5-1.0 mm ²					N2210	10 mm ²						
	HN41525	1.5-2.5 mm ²					N2216	16 mm ²						
	HN446	4-6 mm ²					N2225	25 mm ²						
	HN410	10 mm ²					N2235	35 mm ²						
	HN416	16 mm ²					N2250	50 mm ²						
Copper compression cable lugs (DIN 46235) and connectors (DIN 46267, part 1) acc. to DIN	HD46	6 mm ²		HD5635	6 + 35 mm ²		D226	6 mm ²						
	HD410	10 mm ²		HD51050	10 + 50 mm ²		D2210	10 mm ²						
	HD416	16 mm ²		HD51670	16 + 70 mm ²		D2216	16 mm ²			HD1316	16 mm ²		
	HD425	25 mm ²		HD52595	25 + 95 mm ²		D2225	25 mm ²			HD1325	25 mm ²		
	HD435	35 mm ²		HD5120	120 mm ²		D2235	35 mm ²			HD1335	35 mm ²		
	HD450	50 mm ²		HD5150	150 mm ²		D2250	50 mm ²			HD1350	50 mm ²		
	HD470	70 mm ²		HD5185	185 mm ²		D2270	70 mm ²			HD1370	70 mm ²		
	HD495	95 mm ²					D2295	95 mm ²			HD1395	95 mm ²		
	HD4120	120 mm ²					D22120	120 mm ²			HD13120	120 mm ²		
							D22150	150 mm ²			HD13150	150 mm ²		
							D22185	185 mm ²			HD13185	185 mm ²		
							D22240	240 mm ²			HD13240	240 mm ²		
							D22300	300 mm ²			HD13300	300 mm ²		
Copper solderless terminals (DIN 46234), pin terminals (DIN 46230) acc. to DIN -Cu and connectors (DIN 46341) acc. to DIN	HQ410	10 mm ²		HQ510	10 mm ²		Q2210	10 mm ²						
	HQ416	16 mm ²		HQ516	16 mm ²		Q2216	16 mm ²			HQ1316	16 mm ²		
	HQ425	25 mm ²		HQ525	25 mm ²		Q2225	25 mm ²			HQ1325	25 mm ²		
	HQ435	35 mm ²		HQ535	35 mm ²		Q2235	35 mm ²			HQ1335	35 mm ²		
				HQ550	50 mm ²		Q2250	50 mm ²			HQ1350	50 mm ²		
							Q2270	70 mm ²			HQ1370	70 mm ²		
											HQ1395	95 mm ²		
											HQ13120	120 mm ²		
											HQ13150	150 mm ²		

>>>