



ENGLISH

Datasheet

RS Pro Steel Abrasive Circular Brush, 6000rpm, 178mm Diameter

RS Stock No: **291-1801**



Product Details

RS Pro stainless steel abrasive circular brush has a diameter of 178 mm with a wire diameter of 0.30 mm. It comes with a arbour hole adaptor inserts. It is suitable for heavy duty applications such as descaling and deburring over large surface areas.

Features and Benefits

- High quality industrial crimped filled materials
- 6000 rpm maximum safe speed
- Stainless steel bristle construction
- Arbor fixing type



ENGLISH

Specifications:

Bristle Material	Steel
Fixing Type	Arbour
Bristle Length	38 mm
Diameter	178 mm
Fixing Size	31.75 mm
Maximum Safe Speed	6000 rpm
Suitable For	Heavy Duty Applications such as Descaling & Deburring over Large Surface Areas