

PT-D450VP

18mm Desktop Label Printer

High resolution Backlit display

One touch function keys

Horizontal wide flat
PC style Qwerty keyboard

Includes AC adapter, USB cable
& 18mm Black on white Tze tape (4m)



Top Features:

High resolution backlit monochrome LCD display

- Easy-to-read text and the ability to preview your label before printing.

Logical Step Edit

- Easily edit a label using the one touch keys assigned logically from left to right
- Easy to locate the function that you need

PC Connectable

- Compatible with PT-Editor 5.1
- Windows & Mac drivers available

Horizontally wider PC style keyboard

- Easy to type like on a PC

High Speed Print

- 20mm/second print speed (Max)

Multiple power options

- Supplied with an AC adaptor . Also works with 6 AA batteries (not supplied)

P-touch 18mm Desktop Datasheet

PT-D450VP



General

Carton contents	PT-D450VP labelling machine
	18mm TZe black on white 4m tape cassette
	AC adaptor
	Documentation
	USB-mini cable
	Carry case
Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Brazilian Portuguese, Turkish

Dimensions & Weights

Without carton	(w) x (d) x (h) 0.73 kg
With carton	
Master carton	

Built In Features

Keyboard	65 Key Rubber QWERTY/QWERTZ/AZERTY
Dedicated number keypad	Yes
Interfaces	USB
Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7 to 10.9.
Display type	Backlit High resolution monochrome graphic display
Display resolution	20 characters by 3 lines 320 x 120 dots
Printing speed	Up to 20mm/second
Print resolution	180dpi
Maximum print height	15.8mm
Cutter type	Manual
Label length	30mm minimum 300mm maximum
Maximum lines per label	5 (for 18mm wide tape)
Vertical text printing	Yes
Mirror printing	Yes
Copies	1 to 9
Numbering	Yes (9 times)

Label Creation

Fonts	14 Helsinki, Brussels, US, Los Angeles, San Diego, Florida, Calgary, Belgium, Atlanta, Adams, Brunei, Sofia, Germany, Letter Gothic
Font styles	10 (excl. Normal) Normal, Bold, Outline, Shadow, Solid, Italic, Italic Bold, Italic Outline, Italic Shadow, Italic Solid, Vertical Bold
Font sizes	6, 9, 12, 18, 24, 36, 42 point
Symbols	617
Frames	99
Barcodes	9 CODE39, ITF 2/5, EAN13, EAN8, UPC-A, UPC-E, CODABAR, GS1-128 (UCC/EAN128), CODE128

Memory

Max. characters per label	Max 2,800 characters
Label memory locations	50 areas

Supplies

Tape type	TZe
Tape widths	3.5, 6, 9, 12, 18 mm

Optional Accessories

Batteries	AA alkaline/rechargeable batteries (LR6/HR6) x 6
AC adaptor	AD-E001