



ENGLISH

Datasheet

RS Pro 2.77mm Pitch 25 Way IDC D-sub Connector, Plug, Metal Shell

RS Stock No: **642-4878**



Product Details

RS Pro 25-way IDC D-sub connector has a low profile metal body construction for added durability. This connector has 25 gold plated contacts for precise connection. This straight D-sub male connector has 2.77 mm pitch.

Features and Benefits

- Low profile metal body construction
- 25 number of gold plated contact
- 2.77 mm pitch
- Male plug

**Specifications:**

| | |
|-------------------------------|----------|
| Body Orientation | Straight |
| Contact Plating | Gold |
| Gender | Male |
| Housing Material | Metal |
| Maximum Operating Temperature | +85°C |
| Minimum Operating Temperature | -55°C |
| Number of Contacts | 25 |
| Pitch | 2.77 mm |
| Insulation Supported | No |
| Shell Plating | Tin |