

## Ferrule - AI-TWIN 2X 1 -10 RD - 3200988

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Ferrule, Sleeve length: 10 mm, Length: 17 mm, Color: red




### Why buy this product

- Different versions of the individual TWIN ferrules can be selected for specific applications
- The TWIN ferrules provide a practical way of crimping two conductors in one ferrule
- These special ferrules allow chain bridges to be set up with ease



### Key commercial data

Packing unit	100 pc
Minimum order quantity	100 pc
GTIN	 4 017918 094539
Weight per Piece (excluding packing)	0.17 g
Custom tariff number	85369010
Country of origin	Germany

### Technical data

#### Dimensions

Length (b)	17 mm
Sleeve length	10 mm
Inner dimension of the insulating collar (d)	3.4 mm
Ferrule diameter	2.05 mm
Insulating collar thickness	0.3 mm
Sleeve wall thickness	0.15 mm

#### Ambient conditions

Short-term temperature	120 °C
Max. permanent temperature	105 °C

#### General

Color	red
-------	-----

# Ferrule - AI-TWIN 2X 1 -10 RD - 3200988

## Technical data

### General

Components	free from silicone and halogen
Inflammability class according to UL 94	HB
Material	E-CU

## Classifications

### eCl@ss

eCl@ss 4.0	27060701
eCl@ss 4.1	27060701
eCl@ss 5.0	27400201
eCl@ss 5.1	27400201
eCl@ss 6.0	27400201
eCl@ss 7.0	27400201
eCl@ss 8.0	27400201

### ETIM

ETIM 2.0	EC000005
ETIM 3.0	EC000005
ETIM 4.0	EC000005
ETIM 5.0	EC000005

### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	27121703

## Approvals

### Approvals

---

Approvals

CSA / CSAus / cCSAus

---

Ex Approvals

---

Approvals submitted

---

# Ferrule - AI-TWIN 2X 1 -10 RD - 3200988

## Approvals

### Approval details

CSA

CSAus

cCSAus

## Drawings

