

Datasheet

RS Pro Straight 50 Ω Panel Mount Bulkhead Fitting BNC Connector, jack, Crimp Termination RG58 Silver

RS Stock No: **546-4207**



Product Details

RS Pro panel mount bulkhead fitting BNC connector has a silver plating body, gold plated centre contact and is suitable for RG58 cables. This 50 Ω straight BNC connector comes with cable jack, crimp termination.

Features and Benefits

- Silver plated body
- Gold plated centre contact
- Jack, crimp termination

Specifications:

Body Orientation	Straight
Body Plating	Silver
Bulkhead	Yes
Cable Type	RG58
Contact Material	Copper
Contact Plating	Silver
Gender	Female
Impedance	50 Ω
Mounting Type	Panel Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Crimp
Body Material	Brass
Insulation Material	PTFE
Operating Temperature Range	-65 to +165°C
Standards Met	RoHS Compliant
Voltage Rating	500 V (Working)