

Datasheet

RS Pro Toggle Switch DPDT On-On, 6 A @ 250 V ac, Panel Mount

RS Stock No: **317-601**



Product Details

RS Pro DPDT toggle switch has a locking lever that retains one switch position to prevent accidental switching. This panel mount switch performs on-on operation. It withstands currents up to 6 A at 250 V ac voltage. The fine silver contacts offer superior performance.

Features and Benefits

- Switches with a locking lever
- Silver contacts
- Glass filled polyester case

**Specifications:**

Actuator Length	16.5 mm
Actuator Material	Chrome Plated Brass
Contact Configuration	DPDT
Contact Current Rating	6 A at 250/125 V ac
Contact Material	Silver Plated Copper Alloy
Contact Resistance	10 mΩ
Maximum Operating Temperature	+70°C
Mechanical Life	50000 to 100000 cycles
Minimum Operating Temperature	-20°C
Mounting Type	Panel Mount
Operating Temperature Range	-20 to +70°C
Panel Cut Out Diameter	6.2 mm
Standards Met	CSA Recognised, RoHS Compliant, UL 94V-0 Listed
Switch Operation	On-On
Terminal Type	Solder
Bushing Style	Threaded