

Specifications for Nylon Cloth tape for BMP21-PLUS; BMP21; IDPAL; LABPAL

Adhesive	Permanent Acrylic
Article No.	110893
Brady Material No.	B-499
Material Type	Nylon Cloth
Colour	Black on White
Finish	Matt
Order Reference	M21-375-499
Printable Area - Height (mm)	4800.00
Printable Area - Width (mm)	9.53
Printer Compatibility	BMP21-PLUS; BMP21-LAB; BMP21; IDPAL; LABPAL
Size - Length (m)	4.90
Size - Width (mm)	9.53
Additional Information	High adhesion, Low profile
Thickness (mm)	0.166
Total Qty per Pack	1 Roll(s) / Box
Approval/Compliance	UL Recognised; CSA Accepted
Application	Communication Cabling; Laboratory Identification; Panel Identification; Voice & Data Communication; Wire & Cable Marking
Continuous vs Die Cut Labels	Continuous Tape
Environment	Freezer; Liquid Nitrogen; Autoclave
Industry	Laboratory;Electrical;Healthcare;BuildingsID
Laboratory Application	Bottles, Flasks & Dishes;Centrifuge, Eppendorf & PCR Tubes;Conical & Large Tubes;Cryo Tubes;Cryo Vials;General Identification;Petri Dishes;Well Plates;Vials & Tubes
Description	Nylon cloth labels.
Max. Service Temp. °C	90

