



## Products

### Four-Mandrel Crimping Pliers for turned contacts

97 52 63 DG



97 52 64



97 52 65



97 52 65 DG

### Info Applications

- for crimping turned contacts
- for solder-free electrical connections
- four-mandrel crimping for exact crimping performance
- mandrel gauge to check the basic setting
- locator for positioning the contacts
- repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- these tools have been set precisely (calibrated) in the factory
- optimum transmission of force due to lever action for fatigue-reduced operation
- high operation comfort thanks to handy shape
- all stressed parts are made of special steel, oil-hardened and tempered

#### Model: 97 52 63

- fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- nickel plated head; with two-colour dual component handles

#### Model: 97 52 63 DG

- fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- with digital display of the preset crimping capacities
- display reversible between mm / inch and MIL numerical values
- nickel plated head; with two-colour dual component handles

#### Model: 97 52 64

- pressure adjustment depending on the conductor's diameter by means of adjusting wheel in 4 different positions
- nickel plated head; with two-colour dual component handles

















#### Model: 97 52 65

- fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- nickel plated head; with plastic handles

**Model: 97 52 65 DG**

- o fine adjustment of pressure depending on the conductor's diameter by means of adjusting wheel
- o with digital display of the preset crimping capacities
- o display reversible between mm / inch and MIL numerical values
- o nickel plated head; with plastic handles



Article-No.	EAN 4003773-	Head	Handles	Symbols	Range of Application	Capacity mm <sup>2</sup>	Capacity AWG	Length mm	g	
97 52 63	050148	nickel plated	with two- colour dual component handles	 	turned contacts	0.08 - 2.5	28 - 13	180	360	
97 52 63 DG	063209	nickel plated	with two- colour dual component handles	 	turned contacts	0.08 - 2.5	28 - 13	195	370	
97 52 64	044093	nickel plated	with two- colour dual component handles	 	turned contacts	0.08 - 2.5	28 - 13	180	380	
97 52 65	045236	nickel plated	with plastic handles	 	turned contacts (Harting)	0.14 - 6.0	26 - 10	230	670	
97 52 65 DG	063216	nickel plated	with plastic handles	 	turned contacts (Harting)	0.14 - 6.0	26 - 10	250	690	

technical change and errors excepted

