

Metal Screwless

Double Pole Switches

- Matching metal rockers
- Clear terminal markings
- Colour coded terminals
- Discrete neon
- Neon leads enclosed
- 2 earth terminals
- Captive and backed out terminals
- Terminals have large lead-ins
- In compliance with BS EN 60669-1 or BS 4177 Part 4 where applicable
- 25-year guarantee

20 Amp Double Pole Switches

Chrome/Satin Chrome

Golden Brass/Black Nickel/White

8555CH 20 Amp DP

8555SC

8555GD

8555BN

8555WH

8556CH 20 Amp DP with neon

8556SC

8556GD

8556BN

8556WH

8557CH 20 Amp DP with flex outlet

8557SC

8557GD

8557BN

8557WH



8555GDW



8555BNB



8556WHW



8556SCW



8557BNB



8557GDW

- Chrome and Satin Chrome finish available with either black or white inserts*
- Golden Brass finish available with white inserts only
- Black Nickel finish available with black inserts only
- White finish available with white inserts only

*When ordering, please indicate preference by adding suffix W or B at the end of the catalogue number e.g. 8555CHB would be chrome with black inserts.

Back Boxes
minimum recommended depth

	flush 35mm	dry lining 35mm
20A	DB164	DB2547