






1:1

2:1





Steckbereich ähnlich /  
mating area similar to  
IEC 169-16

Montagedurchbruch /  
Panel cut out



Kabelzuschnitt  
Stripping dimension



Fuer Kabel /  
For cable

| Gr. | Type<br>Typ | ØD1<br>max. | ØD2<br>max. | ØD3<br>max. | ØD4<br>max. | ØD5  | ØD6  | ØD7  | ØD8  | Crimp<br>Aussen/out | Crimp<br>Innen/in |
|-----|-------------|-------------|-------------|-------------|-------------|------|------|------|------|---------------------|-------------------|
| 1   |             |             |             |             |             |      |      |      |      |                     |                   |
| 2   | RG 316 U;   | 2,80        | 2,20        | 1,55        | 0,54        | 1,62 | 2,30 | 3,00 | 4,00 | 3,25                | 0,70              |
| 3   |             |             |             |             |             |      |      |      |      |                     |                   |
| 4   |             |             |             |             |             |      |      |      |      |                     |                   |
| 5   |             |             |             |             |             |      |      |      |      |                     |                   |

**IMS** CONNECTOR  
SYSTEMS

general tolerance  
ISO 2768  
mH

scale: ~~5:1~~ 3:1

Assembly instruction: M-22  
Stripping dimension:

**SN-Chassiskabelbuchse**  
Cable mount bulkhead jack

4526.SN.2812.02'

Rev.  
a

|           |      |             |          |      |
|-----------|------|-------------|----------|------|
| EC_145_08 | a    | Corr. table | 08.09.08 | RSch |
| nr.       | rev. | alteration  | date     | name |