


Solder bucket termination inner diameter: 1,20 mm

Operating voltage < 250 V AC  
 Working current < 7,5 A  
 Insulation resistance > 1GΩ  
 Contact resistance < 15 mΩ  
 Dielectric withstanding voltage 500 V AC / minute

09 64 311 7800	Au Flash	EC00332	11/06/09	PK	HARTING EURL F-95972 Paris		D-Sub, female, straight, 25 poles, tin plated shell, solder buckets, ferrite filter	Maßstab/ Scale 1,5:1