

CAB CAB PC 504020 G3B



Sample photo

Order symbol: CAB PC 504020 G3B
Product nbr: 8113362
Description: Cabinet, PC
Remarks: Locks on the long side

EAN: 6418074020369
EI. number:
 Finland: 3424124
 Electric No. 8212019263
 Denmark:
 Electric No. Italy: 7821055
 Electric No. Sweden: 2539981

Including: Cabinet base, door with PUR gasket, latches, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:			Accessories:	
Length	Width	Height		
mm:	500	400	EKIV 37	DIN-35 Mounting rail
inch:	19.7	15.7	DS35370E1	DIN-35 Mounting rail
Materials:			EKIV 47	DIN-35 Mounting rail
Material:	Polycarbonate		DS35470E1	DIN-35 Mounting rail
Base colour:	RAL 7035 -light grey		FP A 54	Swing-out door/Front plate
Cover colour:	RAL 7035 -light grey		MB 12225 AL	Swing door set
Gasket material:	Polyurethane		FP 54	Front plate
Temperatures:			FP 18X2-54	Front plate
Temperature °C (short term):	-40 ... 120 °C		DRF 54	DIN rail frame set
Temperature °C (continuous):	-40 ... 80 °C		Rating:	
Temperature °F (short term):	-40 ... 250 °F		Ingress Protection (EN 60529): IP65	
Temperature °F (continuous):	-40 ... 175 °F		Impact Resistance (EN 62262): IK08	
Accessories:			Electrical insulation: Totally insulated	
EKIV 54	Mounting plate		Halogen free (DIN/VDE 0472, Part 815): 1	
			UV resistance: UL 508	
			Flammability Rating: UL 746C 5"	
			Glow Wire Test (IEC 695-2-1) °C: 960	
			Certificates:	
			Germanischer Lloyd (GL)	
			SGS Fimko	
			Lloyds Register of Shipping (LR)	
			Gost R	

