

Euromas ABS / PC

Enclosure, ABS




T 245
Order no.: 03245000

Characteristics

Colour	light grey
Colour of enclosure group	Light grey, similar to RAL 7035; special colours on request
Protection class	IP 66
Enclosure material	ABS, PC (UV stabilised) and selected sizes in PC UL 94 V0 (additional UL 94 V0 versions on request), seal made of CR; for details see Technical Information
Scope of delivery	Lid and base, lid screws made of V2A, self-tapping screws for mounting bosses
Note	SV = version with quick-release fastener. IP = Ingress protection acc. to DIN EN 60529

Dimensions



A	340 mm
B	150 mm
C	120 mm
a1	329,3 mm
a2	301,3 mm
b1	139,3 mm
b2	87,3 mm
c1	40 mm
c2	113 mm

Important!

To compensate for pressure when temperatures change and cause moisture in the enclosure, we recommend that you use a [pressure compensation](#) element.

» [Additional information](#)

Technical documentation

Technical drawings	Product drawing in DXF format: 03245000 T 245.dxf (672 KB) 3D product data in STEP format: 03245000 T 245.stp (534 KB) Drawing for mechanical processing: 03245000 T 245-G.dxf (345 KB) Product drawing in PDF format: 03245000 T 245.pdf (103 KB)
Works test certificates	670 WPZ-Euomas PC DE.pdf (197 KB) 670 WPZ-Euomas PC EN.pdf (191 KB)
Technical information	M-V0-02-01 ENG.pdf (55 KB) M-V0-02-01a.pdf (55 KB) T-03-01 ENG.pdf (54 KB) T-03-01a.pdf (55 KB) M-02-02 EN 2012.pdf (54 KB)
Material data	» Important information regarding the following material data

Important information regarding the following material data:

Please note that the information in the material database is based on current knowledge. The tests on basic materials and dyestuffs were carried out and certified by the manufacturers of the material. Changes to the certified values and characteristics may occur during manufacture of the moulding compound and as a result of the addition of any dyestuffs. Any specific or tacit guarantee or warranty or assurance of characteristics or any other liability in connection with the use of the information contained in these certificates is excluded. The customer is not released from the obligation to check whether the materials used correspond to his conditions of use in accordance with the currently valid legal requirements.

×

I have read and agreed to this information.

ABS MMIA Polyman

[Materialdatenblatt deutsch](#)

[Material datasheet english](#)

[UL-Karte/Card](#)

ABS Elix H605

[Materialdatenblatt deutsch](#)

[Material datasheet english](#)

[UL-Karte/Card](#)

ABS Cycolac GPM5500S

[Materialdatenblatt deutsch](#)

[Material datasheet english](#)

[UL-Karte/Card](#)

Downloads

Product brochure	Euomas ABS PC GB.pdf (338 KB)
-------------------------	---

Suitable for the enclosure



Mounting plates, laminated paper (Pertinax), galvanised steel for version 260

22001300

[M](#)

For M/T 244-245



Rubber feet, plug-in

22003300

[E](#)

For M/T 208-260



DIN rails DIN EN 60715 TH 15, galvanised steel

22002720

[TS 15](#)

For M/T 244-245



DIN rails DIN EN 60715 G 32, galvanised steel

22002700

[TS 32](#)

For M/T 244-245



DIN rails DIN EN 60715 TH 35, galvanised steel

22002710

[TS 35](#)

For M/T 244-245



Threaded inserts for mounting bosses

59002810

[DODGE M3x6,5](#)

ND = 4.0 x 6.5

59002820

[DODGE M4x9,5](#)

ND = 5.4 x 9.5



Set of hinges

22006000

[SchM](#)



Screws (SHR) and distance bolts (DIBLZ) for mounting bosses in plastic enclosures

59006101

SHR Z B4,5x7,8

SD = 4.5 / ND = 4.0 / KD = 7.5

* = Available on request