

LOC		DIST				REVISIONS			
G		14		P	F	ZONE	LTR	DESCRIPTION	DATE
							G	REVISED PER 0720-0048-94	6/15/94
								APPD	OK DAP

METRIC

DIMENSIONS LISTED IN mm [INCHES]

AMP WIRE RANGE	 E13288 Listed
16-14 AWG SOLID OR STRANDED	NOT APPLICABLE
 LR7189 Certified	MILITARY P/N AND CLASS
NOT APPLICABLE	NOT APPLICABLE

- 1 STAMP AMP 16-14 APPROX AS SHOWN
- 2 MAXIMUM LENGTH DOES NOT INCLUDE MANUFACTURING TABS
- 3 WIRE BARREL COLOR CODED ORANGE TO DENOTE NICKEL MATERIAL

50	LOOSE PIECE, BOX	8-322347-2
-	LOOSE PIECE	1-322347-0
-	LOOSE PIECE	322347
QTY	PACKAGE TYPE	PART NO
AMP AMP Incorporated Harrisburg, PA 17105-3608		
NAME SPLICE, PARALLEL, HIGH TEMPERATURE, STRATO-THERM™		
SIZE	CAGE CODE	DRAWING NO
C	00779	C=322347
SCALE	10:1	SHEET 1 OF 1

AMP INCORPORATED

CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

MAX RECOMMENDED OPERATING TEMPERATURE: 649°C MAX	VOLTAGE RATING: NOT APPLICABLE	WIRE CROSS SECTIONAL AREA RANGE: 1.04-2.62mm² [2,050-5,180] CIR MILS SOLID OR STRANDED
THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :	DR 4-19-93 TA BRINKMAN
2 PLC DEC ± -	CHK 4-19-93 DA PATTERSON
3 PLC DEC ± -	APPD 4-19-93 DE MILLER
ANGLES ± -	APPD 4-19-93 JL MECKLEY
MATERIAL NICKEL PER ASTM B-162 ANNEALED	PRODUCT SPEC -
FINISH -	APPLICATION SPEC -
WEIGHT -	