

ToLEDo G9/G4/Pygmy

ToLEDo Pygmy 160LM 827 E14 SL

0026844



Range features



PRODUCT OVERVIEW

Ordering number	0026844
Technology	LED
Light colour	830 w arm w hite
Energy class	A+
Average life (Rated) (h)	25000
Lamp shape	Pygmy
Lamp finish	Frosted
Dimmable	No
Cap/Base	E14
Type	ToLEDo Pygmy/ G9/ G4
EAN code	5410288268446
CRI (Ra)	80
Colour temperature (K)	3000
Luminous flux (Rated) (lm)	160
Efficacy (Rated) (lm/w)	40
Watt (Nominal) (W)	2.5
Equivalent watt (W)	15
Voltage (V)	220-240

ToLEDo G9/G4/Pygmy

ToLEDo Pygmy 160LM 827 E14 SL

0026844

DATA TABLE

General data

Dry applications use only	No
Technology	LED
Ordering number	0026844
Energy saving lamp	Yes
Average life (Rated) (h)	25000
Energy class	A+
Average life (Nominal) (h)	25000
Lamp finish	Frosted
Lamp shape	Pygmy
Dimmable	No
Cap/Base	E14
Type	ToLEDo Pygmy/ G9/ G4
EAN code	5410288268446
Product name	ToLEDo Pygmy 160LM 827 E14 SL
Lamp mercury content (mg)	0
Starting time (max) (s)	0.05
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
Control gear required	No
Fixture rating	Open
General application	Hospitality; Residential & Consumer
Intended purpose	General lighting
No. of switching cycles before premature failure (min)	>12500
Special purpose lamp	No
Transformer required	No
Optimal operating condition (°C)	25

Optical data

Light colour	830 w arm w hite
CRI (Ra)	80
Suitable for accent lighting	No
Colour temperature (K)	3000
Luminous flux (Rated) (lm)	160
Luminous flux (Nominal) (lm)	160
Lumen maintenance at end of nominal life (%)	80
Chromaticity coordinate Y	-1
Chromaticity coordinate X	-1
Adjustable chromaticity	No

ToLEDo G9/G4/Pygmy

ToLEDo Pygmy 160LM 827 E14 SL

0026844

Electrical data

kWh per 1000 hours burning time	3
Efficacy (Rated) (lm/w)	40
Watt (Nominal) (W)	2.5
Watt (Rated) (W)	2.5
Equivalent watt (W)	15
Voltage (V)	220-240
Drive current (mA)	24
Lamp power factor	0.4

Physical data

Lamp Length (mm) - C/L	58
Max. Lamp Diameter (mm) - D	27
Lamp dimension equal to filament lamp equivalent	Yes

ENERGY LABEL

