

3521 Kit

Value Range 10R to 1M0

E24 Series 1% Tolerance 50 pcs per value

Each Kit comprising 1 Albums

2176070-1	352110RFT
2176070-2	352111RFT
2176070-3	352112RFT
2176070-4	352113RFT
2176070-5	352115RFT
2176070-6	352116RFT
2176070-7	352118RFT
2176070-8	352120RFT
2176070-9	352122RFT
1-2176070-0	352124RFT
1-2176070-1	352127RFT
1-2176070-2	352130RFT
1-2176070-3	352133RFT
1-2176070-4	352136RFT
1-2176070-5	352139RFT
1-2176070-6	352143RFT
1-2176070-7	352147RFT
1-2176070-8	352151RFT
1-2176070-9	352156RFT
2-2176070-0	352162RFT
2-2176070-1	352168RFT
2-2176070-2	352175RFT
2-2176070-3	352182RFT
2-2176070-4	352191RFT
2-2176070-5	3521100RFT
2-2176070-6	3521110RFT
2-2176070-7	3521120RFT
2-2176070-8	3521130RFT
2-2176070-9	3521150RFT
3-2176070-0	3521160RFT
3-2176070-1	3521180RFT
3-2176070-2	3521200RFT
3-2176070-3	3521220RFT
3-2176070-4	3521240RFT
3-2176070-5	3521270RFT
3-2176070-6	3521300RFT
3-2176070-7	3521330RFT
3-2176070-8	3521360RFT
3-2176070-9	3521390RFT
4-2176070-0	3521430RFT
4-2176070-1	3521470RFT
4-2176070-2	3521510RFT
4-2176070-3	3521560RFT
4-2176070-4	3521620RFT

4-2176070-5	3521680RFT
4-2176070-6	3521750RFT
4-2176070-7	3521820RFT
4-2176070-8	3521910RFT
4-2176070-9	35211K0FT
5-2176070-0	35211K1FT
5-2176070-1	35211K2FT
5-2176070-2	35211K3FT
5-2176070-3	35211K5FT
5-2176070-4	35211K6FT
5-2176070-5	35211K8FT
5-2176070-6	35212K0FT
5-2176070-7	35212K2FT
5-2176070-8	35212K4FT
5-2176070-9	35212K7FT
6-2176070-0	35213K0FT
6-2176070-1	35213K3FT
6-2176070-2	35213K6FT
6-2176070-3	35213K9FT
6-2176070-4	35214K3FT
6-2176070-5	35214K7FT
6-2176070-6	35215K1FT
6-2176070-7	35215K6FT
6-2176070-8	35216K2FT
6-2176070-9	35216K8FT
7-2176070-0	35217K5FT
7-2176070-1	35218K2FT
7-2176070-2	35219K1FT
7-2176070-3	352110KFT
7-2176070-4	352111KFT
7-2176070-5	352112KFT
7-2176070-6	352113KFT
7-2176070-7	352115KFT
7-2176070-8	352116KFT
7-2176070-9	352118KFT
8-2176070-0	352120KFT
8-2176070-1	352122KFT
8-2176070-2	352124KFT
8-2176070-3	352127KFT
8-2176070-4	352130KFT
8-2176070-5	352133KFT
8-2176070-6	352136KFT
8-2176070-7	352139KFT
8-2176070-8	352143KFT
8-2176070-9	352147KFT
9-2176070-0	352151KFT
9-2176070-1	352156KFT
9-2176070-2	352162KFT
9-2176070-3	352168KFT
9-2176070-4	352175KFT

9-2176070-5	352182KFT
9-2176070-6	352191KFT
9-2176070-7	3521100KFT
9-2176070-8	3521110KFT
9-2176070-9	3521120KFT
2176071-1	3521130KFT
2176071-2	3521150KFT
2176071-3	3521160KFT
2176071-4	3521180KFT
2176071-5	3521200KFT
2176071-6	3521220KFT
2176071-7	3521240KFT
2176071-8	3521270KFT
2176071-9	3521300KFT
1-2176071-0	3521330KFT
1-2176071-1	3521360KFT
1-2176071-2	3521390KFT
1-2176071-3	3521430KFT
1-2176071-4	3521470KFT
1-2176071-5	3521510KFT
1-2176071-6	3521560KFT
1-2176071-7	3521620KFT
1-2176071-8	3521680KFT
1-2176071-9	3521750KFT
2-2176071-0	3521820KFT
2-2176071-1	3521910KFT
2-2176071-2	35211M0FT