



ENGLISH

Datasheet

PC Cable Tester

RS Stock number [629-5226](#)



Description:

A compact and portable, versatile cable tester that quickly and reliably checks PC cables using any combination of many of the most popular computer connectors. This powerful troubleshooting tool maps cables and detects good connections and any opens, shorts, and crosses in the cable.

Features:

- Universal tester for all computer cables
- Quickly & easily troubleshoot cables to eliminate the cable as the source of the problem
- True cable mapping
- Easy to read and understand with LED indicator lights
- New rugged case with built-in handle for easy transport Auto scan or manual scan modes.
- Rubber feet grip to desk or bench to prevent slipping
- Power shuts off after 30 seconds of non-use to extend battery life
- Tests over 20 types of patch cables up to 1,000' in length:
 - LAN & telephone
 - Serial
 - Coax 50 & 75* ohm (*Note: up to 600' in length)
 - USB
 - VGA
 - Mini-USB
 - S-video
 - FireWire
 - PS/2 keyboard
 - Parallel printer
- 9V battery included

**Specification:**

- **Maximum Cable Length:**
- **Cable Type Max. Cable Length**
 - D-sub 1,000' (305 m)
 - Phone and data 1,000' (305 m)
 - USB 1,000' (305 m)
 - Firewire 1,000' (305 m)
 - DIN & mini DIN 1,000' (305 m)
 - Centronics 1,000' (305 m)
 - Coax – 50 ohm 1,000' (305 m)
 - Coax – 75 ohm 600' (183 m)
- **Power Requirements:** 9VDC battery (one) included
- **Output Signal:** 8VDC@10mA
- **Auto power-off:** 30 seconds of non-use
- **Dimensions:** 11.0" H X 6.65" W X 1.60" D
- **Weight:** 1.7 lbs.
- **Modular plugs:** RJ45, RJ11, RJ12 shielded & unshielded (UTP/STP)
- **Coaxial:** BNCs and CATV "F"s (BNC-to-F adapter required; not included)
- **D-Sub:** 9-, 15- and 25-pin
- **HD-Sub:** 15-pin
- **USB:** A, B and mini 5-pin
- **1394 firewire:** 4- and 6-pin
- **Mini-DIN:** 4- and 6-pin
- **Centronics:** 36-pin printer