


LOC	DIST	REVISIONS					
IJ	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-06-003670	13 FEB 06	MGR	DB
			A	INITIAL ISSUE	12 SEP 05	MGR	DB



NOTES:

- 1 ATTENUATION $\leq 0,3$ dB, MEASURED AT 1300nm ACC. TO IEC 874-1
 CLAUSE 4.4.7 METHOD 7 EQUILIBRIUM MODE CONDITION

- 2 INDIVIDUAL LENGTH DIFFERENCE ON BOTH SIDES $\leq 50\text{mm}$

- 3 SUPPLY FILLED OUT TEST RESULT SHEET WITH EACH INDIVIDUALLY PACKED ASSEMBLY

- 4 DAT LABEL INFO:

- UNIQUE SERIAL NUMBER
- TYCO LOGO PN
- MANUFACTURING LOCN.


- 5 BLANK LABEL

- 6 CABLE INFO:

- | | |
|-----------------|----------------|
| CORE DIA | – 62,5/125 μm |
| OUTER DIA | – 2,5 x 5,0 mm |
| JACKET COLOR | – ORANGE |
| JACKET MATERIAL | – LSZH |

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (Meter)
X-5349574-Y	XY,0
9-5349574-0	0,5
9-5349574-1	1,5
9-5349574-4	0,4
9-5349574-7	250,0
9-5349574-8	150,0
9-5349574-9	9,5
0-5349574-0	100,0
8-5349574-1	130,0
8-5349574-2	160,0
8-5349574-3	1000,0

2	—	FOAC DAT-85 LABEL	6
4	—	KIT, MM, CER, ASSY, BULK	5
4	—	CRIMP EYELET, BRIGHT TIN	4
2	—	FOAC BOOT 2.5BAY, BLACK	3
2	—	FOAC BOOT 2.5BAY, RED	2
L	—	FOCAB 2.5 62/125 DUPLEX ORANGE	1
Qty	Part Number	Description	Item

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN GIRIYAPPA. M 12 SEP 06		tyco Electronics		Tyco Electronics Corporation FOBU, Bangalore, India	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		FORMM62,5 LEAD 2,5mm TZ ST - ST DPX	
		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± ± -		DIWAKAR BELAVADI 13 FEB 06 DIWAKAR BELAVADI 13 FEB 06 PRODUCT SPEC - APPLICATION SPEC -		SIZE A2	
MATERIAL -		FINISH -		WEIGHT -		CAGE CODE 00779	
				DRAWING NO C-5349574		RESTRICTED TO -	
CUSTOMER DRAWING						SCALE NTS	
						SHEET 1 OF 1	
						REV B	