

HDM501HIHSUVH4



Article Number: 151-07500

Medium Torque Mount, Mounting Hole 0.5", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg



Base Data

Local Order Number HDM501HIHSUVH4

Type HDM501

Color Black (BK)

Features and Benefits

- Mount and tie combination makes it easy to service bundles in the field.
- Made from impact modified, heat stabilized, UV resistant material, ideal for heavy duty environments.
- Eliminates the needs for multiple sized fix diameter clamps.

Product Description This mount, when used with a cable tie eliminates the need to carry multiple sizes of fixed bundle diameter clamps; which reduces inventory and purchasing costs while simplifying the assembly process.

Fixation Method (FF) Screw Mounting and Rivet

Short Description Medium Torque Mount, Mounting Hole 0.5", Max Torque 40.0 lb - ft, PA66HIRHSUV, Black, 500/pkg

Product Dimensions

Length L (imperial) 1.8 "

Length L (metric) 46.0 mm

Width W (imperial) 1.0 "

Width W (metric) 24.0 mm

Cable Tie Width Max (imperial) 0.5 "

Cable Tie Width max. (metric) 12.7 mm

Mounting Hole Diameter D (imperial) 0.5 "

Mounting Hole Diameter D (metric) 12.7 mm

Logistics and Packaging

Quantity per bag

Package Quantity 500

Carton Quantity 500

Weight (Metric) 1 kg

Material and Specifications

Material Polyamide 6.6 high impact modified, heat stabilized, UV resistant (PA66HIRHS)

Material Shortcut PA66HIRHSUV

Flammability UL94 V2

Maximum Torque (kgf-cm) 553 kgf-cm

Maximum Torque (lbf-ft) 40 lbf-ft

Operating Temperature -40 °F to +230 °F (-40 °C to +110 °C)

ROHS Conformity Yes

