

CTK47EU

Bit & Socket Set, Reversible Ratchet Handle with flexible Head, 1/4", 47 pc

Bit and Socket Set 1/4", Reversible Ratchet Handle with flexible head, 47 components.
All sockets are in high quality Chrome-Vanadium and SuperLock-Design,
bits are made from high quality steel and are perfect for almost all applications.
All components are fixed in a handy plastic case.

Order No.: CTK47EU



12 sockets, 1/4",
Chrome-Vanadium and
SuperLock-Design

Ratchet handle 1/4"
with co-molded grip

Extension bar
50 mm

Sliding T-Bar, 115 mm

Universal joint

Bit adapter

Ratchet with 72 teeth

30 bits 1/4" x 25 mm

Content CTK47EU



1	Reversible, ratchet handle with flexible head 1/4", 72 teeth
1	Sliding T-Bar 1/4", length 115 mm
1	Extension bar 1/4", length 115 mm
1	Universal joint 1/4"
1	Bit adapter 1/4" x 25 mm
12	Sockets 1/4": 4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
30	Bits 1/4" x 25 mm
	8 Torx®: T9, T10, T15, T20, T25, T27, T30, T40
	6 Phillips®: PH1(2), PH2(2), PH3(2)
	6 Pozidriv: PZ1(2), PZ2(2), PZ3(2)
	4 Slotted: 3, 4, 5, 6 mm
	6 Hex: 2, 2.5, 3, 4, 5, 6 mm

Order No.	Description	Shelf Pack	EAN
CTK47EU	Bit & Socket Set 1/4", Reversible Ratchet Handle with flexible Head, 47 pc Dimension of case: ca. 24 x 12,5 x 4,5 cm	6	4003019116218