

**M8 female connector straight with cable PUR-OB 3x0,25 black UL, CSA 5m**Female straight  
3-pole**Image**

Vicarious picture

**Approvals****Form**

08041

**Technical Data**

|                               |                                                                  |
|-------------------------------|------------------------------------------------------------------|
| Operating voltage             | max. 60 V AC/DC                                                  |
| Operating current per contact | max. 4 A                                                         |
| Locking of ports              | Screw thread M8 × 1 mm (recommended torque 0.4 Nm) self-securing |
| Protection                    | IP65 and IP67 when plugged and screwed down (EN 60529)           |
| Temperature range             | -25...+85 °C, depending on cable quality                         |

**Cable**

|                            |                          |
|----------------------------|--------------------------|
| No./diameter of wires      | 3 × 0.25 mm <sup>2</sup> |
| Wire isolation             | PP (br, bl, bk)          |
| C-track properties         | 5 million                |
| Jacket                     | PUR (UL/CSA)             |
| Outer diameter             | approx. 4.1 mm           |
| Bend radius (moving)       | 10 x outer diameter      |
| Temperature range (fixed)  | -40...+80 °C             |
| Temperature range (mobile) | -25...+80 °C             |

**Commercial data**

|                                |          |
|--------------------------------|----------|
| Net weight                     | 123      |
| Weight unit                    | Gram     |
| Basic unit                     | pc.      |
| Customs tariff number          | 85444290 |
| Unit (piece)                   | 1        |
| Minimum order quantity (piece) | 1        |

All data on this data sheet was compiled carefully.

Liability regarding correctness, completeness, and actuality is limited to gross negligence. Created: 01/14

**Comments**


Plastic housings with good resistance against chemicals and oils.  
The resistance to aggressive media should be individually tested for your application. Further details on request.  
Further cable lengths on request.

## Contact layout

# Female



## Circuit diagram



Dimension drawing

