

# Product Information



## PVR125x37-Ø12 HL48

EAN 4031582321272

Wheel centre made of Polypropylene, Tread: solid rubber, black, roller bearing

### Technical Data

Wheel diameter	125 mm
Width of Tread	37 mm
Axle Hole Ø	12 mm
Hub length	48 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.468 kg
Load capacity	100 kg
Load capacity (static)	200 kg
Hardness of tread	A 85 Shore



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

