


Item no.: 273-155  
 Product description: Push-wire connector for junction boxes 5-conductor terminal block



Produkt kann von Bild abweichen / product may differ

Packing unit 1000 10\*100 pieces

Product group	7 (Push Wire Conn.)
pole count	5
Cross section [mm <sup>2</sup> ]	0.75 - 1.5 mm <sup>2</sup>
Cross section [AWG]	18 - 16 AWG
Wiring method	e
Connection method	PUSH WIRE®
Number of strands	5
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	18 A
Weight	2.845 g
Color	transparent
Wiring type	Side-entry
No. of connection Points	5
No. of potentials	1
Height	8.6 mm
Height	0.339 in
Width	17.5 mm
Width	0.689 in

Depth  
Depth

18.5 mm  
0.728 in



Strip length from	10 mm
Strip length to	13 mm
Strip length	0.45 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
273-155	ABS	10-HN17750340X	400	24	1,5
273-155	ASTA	Cert.No.167	400	17,5	0,5-1,5
273-155	BV	11941/BO	400	17,5	1,5
273-155	CCA	DK2515	400	17,5	1,5
273-155	CSA	154112-1059435	600	10	20-16
273-155	DEMKO	40677-02	400	17,5	1,5
273-155	DNV	E-9215	400	17,5	1,5
273-155	FIMKO	FI24029	400	17,5	1,5
273-155	GL	17294-00HH	400	17,5	1,5
273-155	KEMA	97.1394.01	400	18	0,5-1,5
273-155	LR	04/20013(E3)	400	17,5	1,5
273-155	NEMKO	P08108775	400	17,5	1,5
273-155	ÖVE	1193-033-01	400	17,5	1,5
273-155	SEMKO	9921002/01-03	400	17,5	1,5
273-155	SEV	10.0146	400	17,5	1,5
273-155	UL	E69654	600	20	20-16
273-155	VDE	40024009	400	17,5	1,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected