



ENGLISH

## Datasheet

### Cable Cutters

# Cable, rod & wire rope cutter pliers



[RS Stock No. 450-3963](#)

**Material:** High carbon steel sheet (k-5) for cut blades, medium carbon steel (s1045c) screws, low carbon steel (s1008c) for rivets, lock lid and body, spring steel for high tension return spring.

**Finish:** Fully polish cut blades, chemical black finish for screws return springs and steel frame, red vinyl coating handle.

**Hardness:** Heat treated to hrc: 56-63 degree (cutting edge), hrc: 38-45 degree (screws) and rivet-hrc: 25 degree up

**Contents:**

7-1/2in (190mm) cable, rod and wire cutter pliers with red vinyl dipping handle. It fits to cut electrical cable, steel strand, high tension steel rope, copper and aluminum rods, (heat-treatment return spring for single-handle operation).

Thickness of blade: 5.0mm

Sheet of serrated action body: 2.0mm