

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14						
			F1	REVISED PER ECR-09-021767	05OCT09	JR	TM




FIGURE 1
FOR .080 TO .125 WIRE INSULATION DIA





FIGURE 2
INSULATION RESTRICTING
FOR .056 TO .110 WIRE INSULATION DIA

1 TONGUE MATERIAL THK IS .031 ± .002

OBSOLETE	1	WIRE TERMINAL INSULATION RESTRICTING	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545) INSULATION: NYLON COLOR: RED (ASTM-D4066) TYPE 1	2-324158-2
	5000	324158 ON TAPE	BODY & SLEEVE: COPPER (ASTM-B152) TIN PL (ASTM-B545)	2-324158-1
	1	WIRE TERMINAL	INSULATION: NYLON COLOR: RED (ASTM-D4066) TYPE 1	324158
	QTY	DESCRIPTION	MATERIAL & FINISH	PART NO

2-324158-2	FIGURE 2	#18		OBSOLETE
324158	FIGURE 1	#22-#16	2-324158-1	
PART NO.	STYLE	WIRE SIZE	PART NO. ON TAPE	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 02OCT09	 Tyco Electronics Corporation Harrisburg, PA 17105-3608			
DIMENSIONS: INCHES		CHK TOM MICHELUTTI 02OCT09	NAME TERMINAL, NYLON – PIDG – RING TONGUE WIRE SIZE: 22-16 —			
	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD MIKE PERCHERKE 02OCT09				
	0 PLC ± — 1 PLC ± — 2 PLC ± — 3 PLC ± .008 4 PLC ± — ANGLES ± .5°	PRODUCT SPEC — APPLICATION SPEC — WEIGHT —				
MATERIAL SEE TABLE	FINISH SEE TABLE	SIZE A2		CAGE CODE 00779	DRAWING NO C-324158	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 10:1		SHEET 1 OF 1		REV F1