

Honeywell Sensing and Control



Search



3455RC 86770001

(Home : Products : Sensors » Thermostats » 3455RC)

[contacts](#)

narrow your search

Products

- Controls Monitoring and Lighting (352)
- Machine Safety (1727)
- Sensors (5910)
- Switches (9781)
- Wireless (45)

Technology

- Capacitive (26)
- Control and Instrumentation (1054)
- Electromechanical (9307)
- Microstructure (1495)
- Thick Film (1409)
- More...

new products

New Wireless Products

Go farther. Work smarter. Explore new possibilities. Just by cutting the cord and making the switch.



Wireless Web Site
WGLA and WPMM
XYR6000™

[find out more](#)

white papers

- Wireless Switches Offer Unlimited Benefit
- Basic Switches Are Not Created Equal
- Applying Precision Switches Sensors for Medical Devices
- New Ways to Measure Torque
- Choosing Safety Switches
- Specifying Hour Meters

Need help?

[Click here to contact us](#)


3455RC Series Ceramic Automatic Reset Thermostats

Actual product appearance may vary.

[Sales & Service](#)
[Distributor Inventory](#)
[Overview](#)
[Specs](#)
[Documentation](#)
[Application Notes](#)

Product Specifications

Functional Properties	Open on rise
Reset Type	Automatic
Amperage	15 A/10 A resistive max.
Voltage	120 Vac/240 Vac
Operating Temperature	0 °C to 260 °C [32 °F to 500 °F]
Environmental Exposure Range	-20 °C to 287 °C [0 °F to 550 °F]
Open Temperature	246.1 °C [475 °F]
Close Temperature	210.0 °C [410 °F]
Open Tolerance	13.9 °C [25 °F]
Close Tolerance	13.9 °C [25 °F]
Dielectric Strength	MIL-STD-202, Method 301; 2000 Vac 60 Hz - Terminal to Case
Insulation Resistance	MIL-STD-202, Method 302; Cond. B - 500 MOhm - 500 Vdc applied
Contact Resistance	MIL-STD-202, Method 307; 0.050 Ohm
Housing Material	Ceramic
Contact Material	Silver/nickel alloy
Agency Approvals and Standards	UL, CSA, VDE
Mounting	B223 10-32 hex cap stud
Series Name	3455RC

[meet dr. larry](#)

VIDEO - Dr. Larry Goldstein explains our newest and best technologies.


[Meet Dr. Larry](#)
[my links](#)
[Login to iCOM](#)
[Login to Rep/AD Portal](#)
[Login to Digital University](#)

News Center

HONEYWELL ADDS NEW 100° AND 180° ARC CONFIGURATIONS TO ITS SMART POSITION SENSOR PORTFOLIO

HONEYWELL INTRODUCES ITS HAWK™ RESOLVERS 1-INCH SERIES, FULLY HOUSED CONFIGURATION

HONEYWELL INTRODUCES MICROPOWER OMNIPOLAR DIGITAL HALL-EFFECT SENSOR ICS WITH LOW SUPPLY VOLTAGE AND ULTRA LOW TYPICAL CURRENT

HONEYWELL EXTENDS ITS TRUSTABILITY® PRESSURE SENSOR PRODUCT LINE WITH A SINGLE SIDE LIQUID MEDIA OPTION

MICRO SWITCH Anniversary site