

## Housing - HC-D 7-TFL-57/O1PG11G - 1660627


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sleeve housing, for single locking latch, height 57 mm, without screw connection, 1 x Pg11, straight cable outlet, zinc die-cast



### Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 017918 137533
Weight per Piece (excluding packing)	72.57 g
Custom tariff number	85389099
Country of origin	Germany

### Technical data

#### Dimensions

Height	57 mm
Width	28 mm
Length	26.5 mm

#### Ambient conditions

Degree of protection of housing (IP)	IP54
	IP65 (with sealing screw)
Ambient temperature (operation)	-40 °C ... 125 °C

#### General

Note	For contact inserts HC-D7, D8, A3, A4, B5, HS2-D7
Type	D7
Housing type	Sleeve housing
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	Straight
Screw connection	none

# Housing - HC-D 7-TFL-57/O1PG11G - 1660627

## Technical data

### General

Type of the screw connection	1x Pg11
Housing material	Zinc die-cast
Housing surface material	Powder-coated, gray

## Classifications

### eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

### ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

### UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

## Approvals

### Approvals

---

Approvals

EAC / GL

---

Ex Approvals

---

Approvals submitted

---

## Housing - HC-D 7-TFL-57/O1PG11G - 1660627

### Approvals

#### Approval details

EAC

GL

### Accessories

#### Accessories

##### Full screw connection

Cable gland - G-INS-PG11-S68N-PNES-GY - 1411142



Cable gland, Cable gland material: Polyamide, External cable diameter 5 mm ... 10 mm, Shielding: No, Connecting thread: Pg11, Color: silver grey

Cable gland - G-INS-PG11-S68N-NNES-S - 1411172



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 5 mm ... 10 mm, Shielding: No, Connecting thread: Pg11, Color: silver

Cable gland - G-INSEC-PG11-S68N-NNES-S - 1411197



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 5 mm ... 10 mm, Shielding: Yes, Connecting thread: Pg11, Color: silver

##### Half screw connection

Pressure screw set - HC-DS-PG11-E - 1675476



Pg pressure screw set, standard version; for housing with Pg11 support; consisting of pressure screw, notched seal and 2 washers

### Mounting material

## Housing - HC-D 7-TFL-57/O1PG11G - 1660627

### Accessories

Sealing screw - HC-D 7-DS-IP65 - 1686229



Sealing screw, for IP65 protection

---

Plug for cable screw gland

Filler plugs - HC-BS-PG11 - 1674493



Filler plugs, for Pg screw connections, type Pg11

---

### Drawings

Dimensioned drawing

