



Specification

CP201 230V 16A/32A Industrial Check Plug



Electrical

Operating voltage range: 200 to 250V AC rms
Frequency response: 30Hz to 70Hz
Power consumption: <1.8W

Open earth indication: earth resistance
>50k Ω nom at 230VAC nom

Open neutral indication: neutral resistance
>50k Ω nom at 230VAC nom

General

Plug type: blue 16A/32A, 3-pin plug to BS EN 60309 (BS 4343)

Power: from mains socket under test

Dimensions: 65 x 65 x 47mm (check plug body)

Weight: 195g approx.

Includes: instructions

Environmental

Temperature (Operating & Storage): -10°C to 40°C, 60% RH Altitude:
up to 2000m

Pollution degree 2

Safety

Conforms to BS EN61010-1, CAT III 300V

Class II, double insulation

EMC

Conforms to BS EN61326-1, BS EN61326-2-2

Check out what else you can get from Martindale:

- 17th Edition Testers
- Accessories
- Calibration Equipment
- Continuity Testers
- Electricians' Kits
- Environmental Products
- Full Calibration & Repair Service
- Fuse Finders
- Digital Clamp Meters
- Digital Multimeters
- Labels
- Microwave Leakage Detectors
- Motor Maintenance Equipment
- Multifunction Testers
- Non-trip Loop Testers
- Pat Testers & Accessories
- Phase Rotation Testers
- Proving Units
- Socket Testers
- Thermometers & Probes
- Test Leads
- Voltage Indicators
- Specialist Metrohm Testers (4 & 5kV)
- Specialist Drummond Testers



Martindale Electric Company Limited
Metrohm House, Penfold Trading Estate, Imperial Way, Watford WD24 4YY, UK
Tel: +44 (0)1923 441717 Fax: +44 (0)1923 446900
E-mail: sales@martindale-electric.co.uk
Website: www.martindale-electric.co.uk



© 2018 Martindale Electric Company Ltd.
Registered in England No. 3387451. Rev 8 LITCP201