

VH AA 1700 CFG



Technical Reference

Specifications

Capacity	1700mAh
Chemistry	NiMH
Dimensions	49.9 x 13.9mm
Maximum Continuous Current	5.1mA
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	0°C
Nominal Voltage	1.2V
Operating Temperature Range	0 → +40°C
Size	AA
Terminal Type	Standard

VH series Ni/MH batteries

Ni/MH batteries

Higher capacitance than NiCd batteries

No memory effect.

Nominal voltage:	1.2 Vdc
Operating temperature under discharge:	-20 °C → +40 °C

Stock no.	housing	format	Dim (mm) Ø x h	Capacity (mAh)
455-8733	VH AA 1700 CFG	AA	14.4 x 50.7	1700
419-9801	VH AAH 1500 CFG	AA	14.4 x 50.7	1500
419-9766	VHCs 3000 CFG	Cs	22.2 x 42.2	3000
455-8755	VH D 9500 CFG	D	32.2 x 60.3	9500