

Datasheet

RS Pro Straight 75Ω Cable Mount BNC Connector Plug, Crimp Termination RG179/U Nickel

RS Stock No: **738-5834**



Product Details

RS Pro straight cable mount BNC connector plug features nickel body plating with brass and gold contacts. This male connector has 75 Ω impedance. It is suitable for a variety of applications including video signalling and test equipment.

Features and Benefits

- Nickel plated body with brass and gold contacts
- Crimp termination method
- Male connector
- Suitable for a variety of applications including video signalling and test equipment

**Specifications:**

Body Orientation	Straight
Body Plating	Nickel
Cable Type	RG179/U
Contact Material	Brass
Contact Plating	Gold
Gender	Male
Impedance	75 Ω
Mounting Type	Cable Mount
Operating Frequency	0 to 2 GHz
Polarity	Normal
Size	Miniature
Termination Method	Crimp
Operating Temperature Range	-40 to +50°C
Standards Met	RoHS Compliant
Voltage Rating	300 V (Working)