

Housing - HC-D 25-TFL-72/O1PG16S - 1672851

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Sleeve housing, for single locking latch, height 72 mm, without screw connection, 1x Pg16, lateral cable entry

The illustration shows version HC-D 25-TFL-72/M 1 PG 16 S



Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 145385
Weight per Piece (excluding packing)	213.74 g
Custom tariff number	85389099
Country of origin	Germany
Note	Made to Order (non-returnable)

Technical data

Dimensions

Height	72 mm
Width	36 mm
Length	79.5 mm

Ambient conditions

Degree of protection of housing (IP)	IP65
Ambient temperature (operation)	-40 °C ... 125 °C

General

Note	For contact inserts HC-D25, A16
Type	D25
Housing type	Sleeve housing
Locking type	for single locking latch
No. of cable outlets	1
Cable exit	Lateral

Housing - HC-D 25-TFL-72/O1PG16S - 1672851

Technical data

General

Screw connection	none
Type of the screw connection	1x Pg16
Housing material	Aluminum die-cast
Housing surface material	Powder-coated, gray
Seal material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27140816
eCl@ss 4.1	27140816
eCl@ss 5.0	27143424
eCl@ss 5.1	27143424
eCl@ss 6.0	27143424
eCl@ss 7.0	27440209
eCl@ss 8.0	27440202

ETIM

ETIM 2.0	EC000437
ETIM 3.0	EC000437
ETIM 4.0	EC000437
ETIM 5.0	EC000437

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals

Approvals

Approvals

EAC / GL

Ex Approvals

Housing - HC-D 25-TFL-72/O1PG16S - 1672851

Approvals

Approvals submitted

Approval details

EAC

GL

Accessories

Accessories

Full screw connection

Cable gland - G-INS-PG16-S68N-PNES-GY - 1411144



Cable gland, Cable gland material: Polyamide, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16

Cable gland - G-INS-PG16-S68N-NNES-S - 1411174



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: No, Connecting thread: Pg16, Color: silver

Cable gland - G-INSEC-PG16-S68N-NNES-S - 1411199



Cable gland, Cable gland material: Brass, nickel-plated, External cable diameter 10 mm ... 14 mm, Shielding: Yes, Connecting thread: Pg16, Color: silver

Plug for cable screw gland

Filler plugs - HC-BS-PG16 - 1674516



Filler plugs, for Pg screw connections, type Pg16

Housing - HC-D 25-TFL-72/O1PG16S - 1672851

Accessories

Drawings

Dimensional drawing

