

# LED LENSER® SEO3 Head Lamp

See and be seen with this affordable, hands-free LED headlamp for style-conscious outdoor enthusiasts. Weighing only 96g and with two-tone styling for cross-gender appeal, it has a washable elastic headband made from hypo-allergenic fabric for maximum comfort over prolonged periods. The headlamp itself includes three bright white LEDs for optimum night-time illumination plus one glare-free red LED to protect night vision. The glow-in-the-dark housing allows wearers to be seen in the dark – a helpful safety feature for runners, walkers and campers. It can be tilted forwards and down within an angle of 90 degrees to make it easier to view and assess any surface or terrain. The SEO lights up to 40 metres in front with a burn time of 40 hours and 90 lumens brightness. Powered by three AAA batteries it features three of LED Lenser's innovative Smart Light Technology settings: Power, Low Power and Signal, giving the user powerful, practical and safe light options for different situations. A useful switch lock prevents auto-operation in transit and it is waterproof up to IPX4 level. Supplied with 3 x AA batteries, washable headband and carabiner.

As a leading international brand of hand-held torches and head lamps, LED Lenser is renowned for superior German engineering, outstanding performance, and state-of-the art technologies, such as the patented Advanced Focus System and Smart Light Technology. Constantly driving innovation to provide class-leading lighting instruments, LED Lenser is the brand of choice for professional tradesmen, emergency services personnel, search & rescue teams and serious outdoor enthusiasts. LED Lenser hand torches and head lamps deliver breath-taking, bright homogenous white light, that turns night into day and simply has to be seen to be believed. Using only the finest materials, such as energy-efficient CREE LED light chips, aircraft-grade aluminium and gold-plated contacts, they are renowned for quality and have a reputation for reliability that is second to none.

- 3 x High End White LEDs
- 1 x Glare-free High End Red LED Light to protect night vision
- Smart Light Technology (SLT) – Power, Low Power, Signal
- Directional Lighting - Lamp Head swivels within an angle of 90 degrees
- Washable, replaceable, anti-allergic headband designed for comfort
- Belt-Hook
- Transport Lock – prevents light accidentally switching on
- Lightweight – ideal for extended duration use
- Casing glows when in use – see and be seen
- IPX6 – superior dust and water protection

## Technical Information

Power: 90 lumens max

Run Time: up to 40 hours

Beam Distance: up to 40m

Weight: 96grams

Supplied with : Belt Hook and Duracell® batteries (3xAAA)

Code	Packaging	Barcode
6103	Test-It	4029113610353