

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [26-03-3151](#)
Status: **Active**
Overview: [KK® Interconnect System - Molex](#)
Description: KK® 3.96mm Crimp Terminal Housing, Use With Trifurcon® Terminals, 15 Circuits

Documents:
[3D Model](#) [Product Specification PS-40-02 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980

General
Product Family Crimp Housings
Series [6442](#)
Application Power, Wire-to-Board
Overview [KK® Interconnect System - Molex](#)
Product Name KK® 396
UPC 800753627048

Physical
Circuits (maximum) 15
Color - Resin Natural
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Material - Resin Nylon
Net Weight 3.900/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm
Stackable No
Temperature Range - Operating See Product Specification

Material Info
Old Part Number 6442-15-Z

Reference - Drawing Numbers
Product Specification PS-40-02
Sales Drawing SD-6442



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[6442Series](#)

Mates With
Molex 3.96mm pitch KK® headers

Use With
[6838](#) , [7258](#) , KK® Trifurcon crimp terminals, [45570](#) MarKK™ terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION